


## Quadri\*Sil Horizontal Line Post Insulator

By OHIO BRASS  
Catalog # [P300095S1070](#)



3" Line Post, Standard Leak, Horizontal Clamptop, Steel Gain Base with 12" and 14" CL holes for 1" bolts.

\*Representative Image

### Features

- Made from hydrophobic silicone polymer

### General

Cantilever Bending Strength - Max.	2700 LB
Cantilever Bending Strength - Routine	1350 LB
Fitting - Ground End	Steel Gain
Fitting - Live Line End	Horizontal Clamp Top
Number of Sheds	79
Shed Style	Uniform

### Dimensions

Angle	14
Diameter - Shed(s)	8.2
Length	17 in
Length - Effective	107.7 in
Rod Diameter	3.000 in
Width	8.07 in

### Electrical Ratings

Arc Distance - Dry	98.2 (2494MM)
Creep and Leakage Distance	298 (7569MM)
Critical Impulse Flashover (CIFO) - Negative	1615
Critical Impulse Flashover (CIFO) - Positive	1515
Flashover Voltage - 60 Hz Dry	965
Flashover Voltage - 60 Hz Wet	890
Voltage Rating	345 kV

### Product Assets

[Catalogs - Quadri\\*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)

[Video - Ohio Brass Insulator Crate Packaging \(VI0816E\)](#)

[Video - Ohio Brass Proper Insulator Handling \(VI08008E\)](#)

[Video - Ohio Brass Polymer Insulator Tester \(VI08041E1015\)](#)