

Quadri*Sil Suspension Insulator

By OHIO BRASS
Catalog # [S025099S201B](#)

25kip Standard leak, Y Ball w/ring



*Representative Image

Features

- Made from hydrophobic silicone polymer

General

Fitting - Ground End	Y-Clevis
Fitting - Live Line End	ANSI Ball
Material	Silicone Rubber
Material - End Fitting	Ductile Iron
Number of Sheds	92
Shed Style	Uniform
Strength Rating - Ultimate	25000 lb
Tensile Strength	25 kip, 5/8" (16 mm)
Tensile Strength - Routine	12,500 lbs
UPC	096359710486

Dimensions

Diameter - Shed(s)	2.9 IN
Length - Effective	111.06 in
Rod Diameter	0.625 in
Thickness - Housing	> 3MM

Electrical Ratings

Arc Distance - Dry	99.3 IN (2522 MM)
Creep and Leakage Distance	253 IN (6426 MM)
Critical Impulse Flashover (CIFO) - Negative	1415 kV
Critical Impulse Flashover (CIFO) - Positive	1395 kV
Flashover Voltage - 60 Hz Dry	940 kV
Flashover Voltage - 60 Hz Wet	855 kV
Voltage Rating	345 kV
Withstand Voltage - 60 Hz Wet	615 kV
Withstand Voltage - Lightning Impulse (Negative)	1580 kV
Withstand Voltage - Lightning Impulse (Positive)	1555 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)
[Test Documents - Prototype Test Report - Quadri*Sil Suspension Insulators - 5/8" Rod \(R17-09-01\)](#)