

HUBBELL

Power Systems

Glass Bell Suspension, 15000 lb CSA

By OHIO BRASS
Catalog # [PCN70146](#)

5-3/4" x 10" Glass Bell Suspension.



Features

- Toughened glass insulator
- Full range of ANSI or CSA class insulators

General

Application	Glass Bell Suspension
Break Strength	45 N·m (400 lb·in)
Fitting - Ground/Base	CS-3 Socket
Fitting - Live Line End	CS-3 Ball
Material	Glass
Material - End Fitting	Galvanized Steel
Strength Rating - Ultimate	15000 lb

Dimensions

Diameter - Bell	255 mm (10")
Height	5.75 in
Weight	7.6 lb

Electrical Ratings

Creep and Leakage Distance	318 mm (12.5")
Critical Impulse Flashover (CIFO) - Negative	130 kV
Critical Impulse Flashover (CIFO) - Positive	125 kV
Flashover Voltage - 60 Hz Dry	80 kV
Flashover Voltage - 60 Hz Wet	50 kV

Certifications And Compliance

Industry Standard(s)	CSA
----------------------	-----

Logistics

Pallet Quantity	1
Standard Package	6

Product Assets

[Catalogs - Toughened Glass Insulators Catalog](#)
[Sales Drawings - Glass Insulator CS-3 \(Reference Only\)](#)



A Hubbell brand