

## PH3 Arrester (228 kV Rated, 7990 mm Creep Distance, AA Hardware)

By OHIO BRASS  
Catalog # [PH3300GH228AA](#)

IEC Station Medium / Polymer Housed Surge Arrester



### Features

- IEC silicone Station Medium class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

### General

Color	Gray
Material	Silicone Polymer Housing
Type	Station

### Electrical Ratings

Frequency Rating	48-62 Hz
Pressure Relief Capability-Symmetrical rms (kA)	63

### Certifications and Compliance

Industry Standard(s) IEC

### Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC \(CA01082E\\_Catalog\\_30\\_0923\\_web\)](#)  
[Installation Manuals - Polymer Hollow Core Station Class Arrester Installation Instructions \(17-5155\)](#)  
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)  
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)  
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)  
[Test Documents - IEC Confirmation of Design Testing PH3 \(TD01110E\)](#)  
[Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)