


HUBBELL Power Systems

Quadri*Sil Suspension Insulator

By OHIO BRASS

Catalog # [S030030S2010](#)

30kip Standard leak, Y Ball



*Representative Image

Features

Made from hydrophobic silicone polymer

General

EU RoHS Indicator	Contact Manufacturer
Fitting - Ground End	Y-Clevis
Fitting - Live Line End	ANSI Ball
Material	Silicone Rubber
Material - End Fitting	Ductile Iron
Number of Sheds	28
Shed Style	Uniform
Strength Rating - Ultimate	30000 lb
Tensile Strength	30 kip, 5/8" (16 mm)
Tensile Strength - Routine	15,000 lbs
UPC	096359443667

Dimensions

Diameter - Shed(s)	2.9 IN
Length - Effective	41.94 in
Rod Diameter	0.625 in
Thickness - Housing	> 3MM

Electrical Ratings

Arc Distance - Dry	30.2 IN (766 MM)
Creep and Leakage Distance	77 IN (1956 MM)
Critical Impulse Flashover (CIFO) - Negative	430 kV
Critical Impulse Flashover (CIFO) - Positive	445 kV
Flashover Voltage - 60 Hz Dry	315 kV
Flashover Voltage - 60 Hz Wet	305 kV
Withstand Voltage - 60 Hz Wet	190 kV
Withstand Voltage - Lightning Impulse (Negative)	510 kV
Withstand Voltage - Lightning Impulse (Positive)	525 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)
[Sales Drawings - S030030S2010 \(Reference Only\)](#)
[Test Documents - Prototype Test Report - Quadri*Sil Suspension Insulators - 5/8" Rod](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-S030030S2010-SPEC-EN | REV 6/2024