

PH4 Arrester (36 kV Rated, 2130  
mm Creep Distance, AA Hardware)

By OHIO BRASS  
Catalog # [PH4036GM036AA](#)

IEC Station High / Polymer Housed Surge Arrester

Features

- IEC silicone Station High class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Catalog Number	PH4036GM036AA
Color	Gray Housing
Material	Silicone Polymer Housing
Type	Station
UPC	096359834120

Electrical Ratings

Frequency Rating	48-62 Hz
------------------	----------



Pressure Relief Capability- 63  
Symmetrical rms (kA)

Certifications And Compliance

Industry Standard(s) IEC

Product Assets

- [Catalogs - Station Class Surge Arresters IEEE and IEC](#)
- [Installation Manuals - Polymer Hollow Core Station Class Arrester](#)
- [Installation Instructions](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Specifications - PH4036GM036AA](#)
- [Specifications - Specification for Hollow Core IEC Station Class Arresters](#)
- [Test Documents - IEC Confirmation of Design Testing PH4](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)