

PH4 Arrester (396 kV Rated, 13110 mm Creep Distance, AA Hardware)

By OHIO BRASS
Catalog # [PH4420GV396AA](#)

IEC Station High / Polymer Housed Surge Arrester

Features

- IEC silicone Station High class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Catalog Number	PH4420GV396AA
Color	Gray Housing
Material	Silicone Polymer Housing
Type	Station
UPC	096359829898

Electrical Ratings

Frequency Rating	48-62 Hz
------------------	----------



Pressure Relief Capability- 63
Symmetrical rms (kA)

Certifications And Compliance

Industry Standard(s) IEC

Product Assets

- [Catalogs - Station Class Surge Arresters IEEE and IEC](#)
- [Installation Manuals - Polymer Hollow Core Station Class Arrester Installation Instructions](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Specifications - PH4420GV396AA](#)
- [Specifications - Specification for Hollow Core IEC Station Class Arresters](#)
- [Test Documents - IEC Confirmation of Design Testing PH4](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)