

HUBBELL

Power Systems

Glass Bell Suspension w/ Zinc Sleeve, 40000 lb

By OHIO BRASS
Catalog # [PSN180146DC](#)

5-3/4" x 11" Glass Bell Suspension w/ Zinc Sleeve.



Features

- Dielectric made of toughened glass, hot-dip galvanized ductile iron cap and forged steel pin, stainless steel split pin for coupling of units
- Easy inspection and mechanical reliability
- High thermal and mechanical resistance
- Reduced aging
- High dielectric resistance and homogenous potential distribution

General

Application	Glass Bell Suspension
Break Strength	47 N·m (400 lb·in)
Fitting - Ground/Base	52-8-H Socket
Fitting - Live Line End	52-8-H Ball
Material	Glass
Material - End Fitting	Galvanized Steel w/ Zinc Sleeve
Strength Rating - Ultimate	40000 lb
UPC	096359683339

Dimensions

Diameter - Bell	11" (280 mm)
Dimensions	11 in x 11 in x 6.3 in
Height	6.3 in
Length	11 in
Weight	13.5 lb
Width	11 in

Electrical Ratings

Creep and Leakage Distance	15" (381 mm)
Critical Impulse Flashover (CIFO) - Negative	130 kV
Critical Impulse Flashover (CIFO) - Positive	125 kV
Flashover Voltage - 60 Hz Dry	80 kV
Flashover Voltage - 60 Hz Wet	50 kV

Certifications And Compliance

Industry Standard(s)	ANSI C.29.2.B
----------------------	---------------

Logistics

Pallet Quantity	90
Standard Package	6

Product Assets

[Catalogs - Toughened Glass Insulators Catalog](#)
[Sales Drawings - Glass Insulator 52-8-H \(Reference Only\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-PSN180146DC-SPEC-EN | REV 6/2024