

**Porcelain Pin Type Insulator ANSI  
56-2**

By OHIO BRASS  
Catalog # [PSPT562](#)



Porcelain Pin Type Insulator for distribution applications.

\*Representative Image

**Features**

- Manufactured according to ANSI C29.6
- Supports low to medium voltage lines
- Capable of withstanding physical stress and environmental factors, prolonging service life
- Designed to perform under varieties of weather conditions
- Ideal for both urban and rural power distribution networks

**Application**

Pin Type

**General**

Cantilever Bending Strength - Max.	3000
Catalog Number	PSPT562
Fitting - Ground/Base	1-3/8" Pin Hole Diameter
Fitting - Live Line End	K - Neck
Insulator Type	56-2
Material	Porcelain
UPC	096359832171

**Dimensions**

Diameter - Shed(s)	9.10 in
Dimensions	9.10 in x 9.10 in x 6.5 in

Height	6.5 in
Length	9.1 in
Weight	6 lb
Width	9.1 in

**Electrical Ratings**

Arc Distance - Dry	8.3 in (210 mm)
Creep and Leakage Distance	17.0 in (432 mm)
Critical Impulse Flashover (CIFO) - Positive	175 kV
Flashover Voltage - 60 Hz Dry	110 kV
Flashover Voltage - 60 Hz Wet	70 kV
Voltage Rating	23 kV

**Certifications And Compliance**

Industry Standard(s)	ANSI C29.6
----------------------	------------

**Logistics**

Pallet Quantity	112
-----------------	-----

**Product Assets**

[Catalogs - Porcelain Pin Type Insulators](#)  
[Literature - Porcelain Pin Type Insulators](#)  
[Sales Drawings - PSPT562](#)  
[Specifications - PSPT562](#)