

Porcelain Pin Type Insulator ANSI
56-3

By OHIO BRASS
Catalog # [PSPT563](#)



*Representative Image

Features

- Manufactured according to ANSI C29.6
- Supports low to medium voltage lines
- Capable of withstanding physical stress and environmental factors, prolonging service life
- Designed to perform under varieties of weather conditions
- Ideal for both urban and rural power distribution networks

Application

Pin Type

General

Cantilever Bending Strength - Max.	3000
Catalog Number	PSPT563
Fitting - Ground/Base	1-3/8" Pin Hole Diameter
Fitting - Live Line End	K - Neck
Insulator Type	56-3
Material	Porcelain
UPC	096359832188

Dimensions

Diameter - Shed(s)	10.50 in
Dimensions	10.50 in x 10.50 in x 7.30 in

Height	7.3 in
Length	10.5 in
Weight	18.7 lb
Width	10.5 in

Electrical Ratings

Arc Distance - Dry	9.5 in (241 mm)
Creep and Leakage Distance	21.0 in (553 mm)
Critical Impulse Flashover (CIFO) - Positive	200 kV
Flashover Voltage - 60 Hz Dry	125 kV
Flashover Voltage - 60 Hz Wet	80 kV
Voltage Rating	34.5 kV

Certifications And Compliance

Industry Standard(s)	ANSI C29.6
----------------------	------------

Logistics

Pallet Quantity	64
-----------------	----

Product Assets

[Catalogs - Porcelain Pin Type Insulators](#)
[Literature - Porcelain Pin Type Insulators](#)
[Sales Drawings - PSPT563](#)
[Specifications - PSPT563](#)