

HUBBELL

Power Systems

Strand Mount Aerial Slack Storage System, 10" Dia.

By Opti-Loop
Catalog # [FOS10TMK](#)

OptiLoop 10.125" Strand Mount Aerial Slack Storage System, 6005 Alloy Aluminum, Dual coat baked on polyester powder coat



*Representative Image

Features

- 6005 alloy aluminum construction with continuous welds at cross bars and ends
- Dual coat baked on polyester powder coat finish
- Tie eyelets accommodate both stainless steel and plastic ties.
- Radius ends ensure no sharp corners.
- The outward-facing channel design and minimal surface area minimizes stress and ice loading.
- Aluminum brackets and bugnuts with galvanized nuts and bolts

General

| | |
|------------------|--|
| Application | Strand/Messenger Cable storage |
| Cable Tie Eyelet | Yes |
| Finish Type | Dual Coat Baked On Polyester Powder Coat |
| Material | 6005 Alloy Aluminum |
| Product Category | Communications Connectors |
| UPC | 096359706953 |
| Wraps | Single |

Dimensions

| | |
|--------------------|-----------|
| Diameter - Inside | 10.125 in |
| Diameter - Outside | 11.4 in |
| Height | 0.65 in |
| Length | 23 in |
| Weight | 3.5 lb |

Conductor Related

| | |
|------------------------------|------------------|
| Conductor Type | Messenger Strand |
| Messenger Diameter - Maximum | 0.25 in |
| Messenger Diameter - Minimum | 0.313 in |

Logistics

| | |
|-----------------|-----|
| Pallet Quantity | 180 |
|-----------------|-----|

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Catalogs - Opti-Loop Storage Systems](#)
- [Literature - Opti-Loop FOS](#)
- [Sales Drawings - CC-21800](#)
- [Video - Hubbell Power Systems In Depth: Opti-loop Plastic vs Aluminum](#)
- [Video - Opti-Loop® Lashed Aerial Installation](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OPT-FOS10TMK-SPEC-EN | REV 6/2024