

Communications Connectors
Hardware

By OPTILOOP
Catalog # [FOSBN250](#)



OptiLoop Strand/Messenger Bugnut Hardware, Aluminum
Clamping Plates with Galvanized Nut and Bolt, Qty 250 Pieces

Features

- 6063 alloy aluminum clamping plates
- Galvanized steel nut and bolt
- Sold as box of 250 pieces

Application

Attaches hardware to the messenger

General

Material	6063 Alloy Aluminum with Galvanized Nut and Bolt
Product Category	Communications Connectors
UPC	096359599944

Dimensions

Dimensions	10.250 in x 9.500 in x 7.000 in
Height	7.000 in
Length	10.250 in
Weight	31.800 lb
Width	9.500 in

Conductor Related

Conductor Type	Messenger Strand
Messenger Diameter - Maximum	0.250 in
Messenger Diameter - Minimum	0.313 in

Product Assets

[Catalogs - Opti-Loop Storage Systems \(CA05037E\)](#)
[Sales Drawings - CC-23351](#)

Related Products

[TMK - TMK Tap Mounting Kit](#)
[ATB255050 - Tap Bracket, 2 1/2", Qty 50 Pieces](#)

