

Strand Mount Aerial Slack Storage System, 12" Dia. Plastic

By Opti-Loop
Catalog # [FOSPI2TMKBABA](#)



OptiLoop 12.00" Strand Mount Aerial Slack Storage System, 25% calcium carbonate filled impact copolymer polypropylene

Features

- 25% calcium carbonate filled impact copolymer polypropylene construction
- Aluminum brackets and bugnuts with galvanized nuts and bolts
- Stainless steel mounting hardware

Application

Strand/Messenger Cable storage

General

Catalog Number	FOSPI2TMKBABA
Material	25% calcium carbonate filled impact copolymer polypropylene

Dimensions

Diameter - Inside	12 in
Diameter - Outside	13.6 in
Dimensions	17.438 in x 14.063 in x 3.000 in
Height	3 in
Length	17.438 in
Weight	3.2 lb
Width	14.063 in

Conductor Related

Conductor Diameter - Maximum	0.313 in
Conductor Diameter - Minimum	0.25 in
Conductor Diameter Range	0.25 - 0.313
Conductor Type	Messenger Strand
Messenger Diameter - Maximum	0.25 in
Messenger Diameter - Minimum	0.313 in

Certifications And Compliance

Buy America(n) Qualified	BABA Compliant (All status valid till December 2025)
--------------------------	--

Logistics

Pallet Quantity	200
-----------------	-----

Product Assets

- [Catalogs - Opti-Loop Storage Systems](#)
- [Sales Drawings - CC-21802](#)
- [Specifications - FOSPI2TMK](#)
- [Video - Hubbell Power Systems In Depth: Opti-loop Plastic vs Aluminum](#)
- [Video - Opti-Loop® Lashed Aerial Installation](#)