

PRC 85 Series Bushing - 15kV

By PCORE Electric
Catalog # B-85112-70

PRC® 15kV-1200A Transformer-Circuit Breaker Bushing, Paper-Resin-Capacitor Type, Rated per CSA C88.1, Bottom Connected for Air-to-Oil Applications, 10.00" Min. Oil Immersion Level



*Representative Image

Features

- Resin-impregnated paper wound core with external porcelain insulator
- High creep upper porcelain, High seismic

Application

Transformer-Oil Circuit Breaker

General

Bottom Terminal Type	Threaded
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Porcelain
Mounting Position	Vertical
Number of Flange Mounting Holes	4
Test Tap	Yes
Top Terminal Plating	Silver Plated
Top Terminal Type	Threaded
Type	Condenser Bushings

Dimensions

Above Flange Length	15.62 in
Below Flange Length	16.88 in
Diameter - Below Flange Maximum D <gt;/> 1"	3.12 in
Diameter - Below Flange Maximum P	3.38 in
Diameter - Bottom Terminal Outside	1 1/2-12
Diameter - Live Part Top	3.88 in
Diameter - Top Terminal Outside	1 1/2-12
Effective Length - Bottom Terminal	2.12 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.50 in
Length	32.50 in
Length - Ground Shield	10.00 in
Length - Live Part Top	4.06 in
Length - Minimum Oil Immersion Level	10.00 in
Sealing Surface Outside Diameter	6.25 in
Weight	37 lb

Electrical Ratings

BIL	110 kV
Current Rating	1200 A
Minimum Creepage	21 in
Minimum Strike	10.00 in
kV Class	15 kV

Certifications and Compliance

Industry Standard(s)	CSA
----------------------	-----

Product Assets

[Installation Manuals - Instruction Manual for PRC® Bushings \(B-303339 rev 07-14-20\)](#)
[Sales Drawings - PRC Bushing \(85112_and_70\)](#)

Related Products



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
PCOR-B-85112-70-SPEC-EN | REV 1/2024