

HUBBELL Power Systems

Quadri*Sil Suspension Insulator

By OHIO BRASS

Catalog # [S030047S201A](#)

30kip Standard leak, Y Ball w/ring



*Representative Image

Features

Made from hydrophobic silicone polymer

General

EU RoHS Indicator	Contact Manufacturer
Fitting - Ground End	Y-Clevis
Fitting - Live Line End	ANSI Ball
Material	Silicone Rubber
Material - End Fitting	Ductile Iron
Number of Sheds	44
Shed Style	Uniform
Strength Rating - Ultimate	30000 lb
Tensile Strength	30 kip, 5/8" (16 mm)
Tensile Strength - Routine	15,000 lbs
UPC	096359594970

Dimensions

Diameter - Shed(s)	2.9 IN
Dimensions	60.31 in x 8 in x 8 in
Height	8 in
Length	60.31 in
Length - Effective	59.22 in
Rod Diameter	0.625 in
Thickness - Housing	> 3MM
Weight	10.8 lb
Width	8 in

Electrical Ratings

Arc Distance - Dry	47.4 IN (1205 MM)
Creep and Leakage Distance	121 IN (3073 MM)
Critical Impulse Flashover (CIFO) - Negative	685 kV
Critical Impulse Flashover (CIFO) - Positive	690 kV
Flashover Voltage - 60 Hz Dry	490 kV
Flashover Voltage - 60 Hz Wet	465 kV
Withstand Voltage - 60 Hz Wet	295 kV
Withstand Voltage - Lightning Impulse (Negative)	785 kV
Withstand Voltage - Lightning Impulse (Positive)	790 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog](#)
[Sales Drawings - S030047S201A \(Reference Only\)](#)
[Test Documents - Prototype Test Report - Quadri*Sil Suspension Insulators - 5/8" Rod](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-S030047S201A-SPEC-EN | REV 6/2024