

Quadri*Sil Suspension Insulator

By OHIO BRASS
Catalog # [S030056S3010](#)

30kip Standard leak, Socket Ball



*Representative Image

Features

- Made from hydrophobic silicone polymer

General

EU RoHS Indicator	Contact Manufacturer
Fitting - Ground End	ANSI Socket
Fitting - Live Line End	ANSI Ball
Material	Silicone Rubber
Material - End Fitting	Ductile Iron
Number of Sheds	52
Shed Style	Uniform
Strength Rating - Ultimate	30000 lb
Tensile Strength	30 kip, 5/8" (16 mm)
Tensile Strength - Routine	15,000 lbs
UPC	096359599111

Dimensions

Diameter - Shed(s)	2.9 IN
Length - Effective	66.69 in
Rod Diameter	0.625 in
Thickness - Housing	> 3MM

Electrical Ratings

Arc Distance - Dry	56.1 IN (1424 MM)
Creep and Leakage Distance	143 IN (3632 MM)
Critical Impulse Flashover (CIFO) - Negative	810 kV
Critical Impulse Flashover (CIFO) - Positive	810 kV
Flashover Voltage - 60 Hz Dry	585 kV
Flashover Voltage - 60 Hz Wet	545 kV
Voltage Rating	138/161 kV
Withstand Voltage - 60 Hz Wet	350 kV
Withstand Voltage - Lightning Impulse (Negative)	935 kV
Withstand Voltage - Lightning Impulse (Positive)	935 kV

Product Assets

[Catalogs - Quadri*Sil Suspension & Line Post Insulators Catalog \(CA08051E\)](#)
[Test Documents - Prototype Test Report - Quadri*Sil Suspension Insulators - 5/8" Rod \(R17-09-01\)](#)