

HUBBELL

Power Systems

PRC type bushing - 69kV

By PCORE Electric
 Catalog # [B-08959320070](#)

PRC® 69kV- 400/1200A Transformer-Circuit Breaker Bushing, Paper-Resin-Capacitor Type, Rated per IEEE C57.19.01, Draw lead or Bottom connected for Air-to-Oil Applications , 21.00" Min. Oil Immersion Level



Features

- Resin-impregnated paper wound core with external porcelain insulator
- High creep upper porcelain, High seismic

General

Application	Transformer-Oil Circuit Breaker
Bottom Terminal Type	2-Hole NEMA Pad
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Porcelain
Mounting Position	Vertical
Number of Flange Mounting Holes	6
Test Tap	Yes
Top Terminal Plating	Silver Plated
Top Terminal Type	Threaded
Type	Condenser Bushings

Dimensions

Above Flange Length	36.88 in
Below Flange Length	44 in
Diameter - Below Flange Maximum D <gt/> 1"	4.00 in
Diameter - Below Flange Maximum P	4.50 in
Diameter - Live Part Top	4.50 in
Diameter - Top Terminal Outside	1 1/2-12
Dimensions	71.88 in x 10.63 in x 71.88 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	9.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	10.62 in
Height	71.88 in
Length	71.88 in
Length - Drawlead Above Flange	33.00 in
Length - Ground Shield	21.00 in
Length - Live Part Top	5.81 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Outside Diameter	8.25 in
Weight	139 lb
Width	10.63 in

Electrical Ratings

BIL	350 kV
Current Rating	1200 A
Minimum Creepage	69.5 in
Minimum Strike	30 in
kV Class	69 kV

Certifications And Compliance

Industry Standard(s)

IEEE

Product Assets

[Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)

[Installation Manuals - Instruction Manual for PRC® Bushings](#)

[Literature - Quick-Links - PCORE](#)

[Sales Drawings - PRC Bushing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
PCOR-B08959320070-SPEC-EN | REV 6/2024