

# HUBBELL

## Power Systems

### POC 88 Series Bushing - 25kV

By PCORE Electric  
 Catalog # [B-88743-70](#)

POC® 25kV-4000A Transformer-Circuit Breaker Bushing, Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21.00" Min. Oil Immersion Level



\*Representative Image

#### Features

- Paper oil capacitor wound core with external porcelain insulator
- High seismic

#### General

Application	Transformer-Oil Circuit Breaker
Bottom Terminal Type	Threaded
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Porcelain
Mounting Position	Vertical
Number of Flange Mounting Holes	6
Test Tap	Yes
Top Terminal Plating	Silver Plated
Top Terminal Type	Threaded
Type	Condenser Bushings

#### Dimensions

Above Flange Length	20.12 in
Below Flange Length	30.5 in
Diameter - Below Flange Maximum D <gt;/> 1"	5.25 in
Diameter - Below Flange Maximum P	6.00 in
Diameter - Bottom Terminal Outside	3-12
Diameter - Live Part Top	9.25 in
Diameter - Top Terminal Outside	3-12
Dimensions	50.62 in x 11.00 in x 50.62 in
Effective Length - Bottom Terminal	3.00 in
Effective Length - Top Terminal	3.00 in
Flange Mounting Hole Bolt Circle	9.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	11 in
Height	50.62 in
Length	50.62 in
Length - Ground Shield	21.00 in
Length - Live Part Top	6.25 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Outside Diameter	8.25 in
Weight	141 lb
Width	11 in

#### Electrical Ratings

BIL	150 kV
Current Rating	4000 A
Minimum Creepage	19.5 in
Minimum Strike	11 in
kV Class	25 kV

## Certifications And Compliance

Industry Standard(s) IEEE

## Product Assets

[Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)

[Installation Manuals - Instruction Manual for POC® Bushings](#)

[Sales Drawings - POC Bushing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
PCOR-B8874370-SPEC-EN | REV 6/2024