

PRC 89 Series Quick-Link Bushing - 25kV

By PCORE Electric
Catalog # [B-89253-200-70](#)

PRC® 25kV-2000A Quick-Link™ Transformer Bushing, Paper-Resin-Capacitor Type, Rated per IEEE C57.19.01, Draw-Lead/Bottom Connected for Air-to-Oil Applications, 21.00" Min. Oil Immersion Level



*Representative Image

Features

- Resin-impregnated paper wound core with external porcelain insulator
- High creep upper porcelain, High seismic

Application

Transformer-Oil Circuit Breaker

General

Bottom Terminal Type	2-Hole NEMA Pad
Catalog Number	B-89253-200-70
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Porcelain
Mounting Position	Vertical
Number of Flange Mounting Holes	4
Test Tap	Yes
Top Terminal Plating	Silver Plated
Top Terminal Type	Threaded
Type	Condenser Bushings

Dimensions

Above Flange Length	20.62 in
Below Flange Length	36 in
Diameter - Below Flange Maximum D <gt/> 1"	4.00 in
Diameter - Below Flange Maximum P	4.50 in
Diameter - Live Part Top	4.50 in
Diameter - Top Terminal Outside	2-12

Dimensions	56.62 in x 10.62 in x 56.62 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	10.62 in
Height	56.62 in
Length	56.62 in
Length - Drawlead Above Flange	16.75 in
Length - Ground Shield	21.00 in
Length - Live Part Top	5.81 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Outside Diameter	6.25 in
Weight	90 lb
Width	10.62 in

Electrical Ratings

BIL	150 kV
Current Rating	2000 A
Minimum Creepage	27.5 in
Minimum Strike	14 in
kV Class	25 kV

Certifications And Compliance

Industry Standard(s)	IEEE
----------------------	------

Product Assets

[Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
[Installation Manuals - Instruction Manual for PRC® Bushings](#)
[Literature - Quick-Links - PCORE](#)
[Sales Drawings - PRC Bushing](#)
[Specifications - B8925320070](#)