

HUBBELL Power Systems

PRC 89 Series Bushing - 46kV

By PCORE Electric
Catalog # [B-89411-70](#)

PRC® 46kV-1200A Transformer-Circuit Breaker Bushing, Paper-Resin-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 16.50" Min. Oil Immersion Level



*Representative Image

General

Application	Transformer-Oil Circuit Breaker
Bottom Terminal Type	Threaded
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Porcelain
Mounting Position	Vertical
Number of Flange Mounting Holes	4
Test Tap	Yes
Top Terminal Plating	Silver Plated
Top Terminal Type	Threaded
Type	Condenser Bushings

Dimensions

Above Flange Length	26.88 in
Below Flange Length	31.5 in
Diameter - Below Flange Maximum D <gt/> 1"	4.00 in
Diameter - Below Flange Maximum P	4.50 in
Diameter - Bottom Terminal Outside	1 1/2-12
Diameter - Live Part Top	4.50 in
Diameter - Top Terminal Outside	1 1/2-12
Effective Length - Bottom Terminal	2.12 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	8.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	10.62 in
Length	58.38 in
Length - Ground Shield	16.50 in
Length - Live Part Top	4.06 in
Length - Minimum Oil Immersion Level	16.50 in
Sealing Surface Outside Diameter	7.25 in
Weight	106 lb

Electrical Ratings

BIL	250 kV
Current Rating	1200 A
Minimum Creepage	49 in
Minimum Strike kV Class	21 in 46 kV

Certifications And Compliance

Industry Standard(s)	IEEE
----------------------	------

Product Assets

[Installation Manuals - Instruction Manual for PRC® Bushings](#)

[Sales Drawings - PRC Bushing](#)



A Hubbell brand