

SVNH Arrester (245 kV MCOV)

By OHIO BRASS
Catalog # [SVNH312GA245AA](#)

IEEE Station Class Polymer Housed High Strength Surge Arrester



Features

- IEEE silicone station class arrester
- IEEE 693 High Performance Qualification
- high strength alternative to the SVN arrester
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Catalog Number	SVNH312GA245AA
Color	Gray Housing
Type	Station
UPC	096359828204

Dimensions

Height	122 in
Maximum Operating Altitude	12000 ft
Minimum Mounting Spacing on Center (Sea Level) - Phase to	1770
Minimum Mounting Spacing on Center (Sea Level)- Phase to Phase	2018
Weight	710 lb

Electrical Ratings

Creep and Leakage Distance	326 in
Frequency Rating	48-62 Hz
MCOV	245 kV
Maximum .5 Microsecond Discharge Volts @ Classifying	911 kV

Current

Maximum Discharge Voltage	<ul style="list-style-type: none">• 632 kV @ 1.5 kA• 654 kV @ 3 kA• 677 kV @ 5 kA• 711 kV @ 10 kA• 758 kV @ 20 kA• 834 kV @ 40 kA
---------------------------	--

Maximum Switching Surge Protective Level @ 500A	584 kV
Rating - KVA	312
Voltage - Line	362 V
Withstand Voltage - 60 Hz Wet	590
Withstand Voltage - Lightning	1327
Impulse	
Withstand Voltage - Switching	981
Impulse	

Certifications And Compliance

Industry Standard(s)	IEEE
----------------------	------

Product Assets

- [Catalogs - Station Class Surge Arresters IEEE and IEC](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - SVNH Substation Arresters](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Literature - Polymer Station Arrester](#)
- [Sales Drawings - SVNH312GA245AA \(For Reference Only\)](#)
- [Specifications - SVNH312GA245AA](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)