

HUBBELL

Power Systems

POC Series II Bushing - 230kV

By PCORE Electric
 Catalog # [POC900G2500SX17](#)

POC® 230kV-2500A Transformer-Circuit Breaker Bushing, Paper-Oil-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 26.75" Min. Oil Immersion Level



Features

- Paper oil capacitor wound core with external porcelain insulator
- High creep upper porcelain, High seismic

General

Application	Transformer-Oil Circuit Breaker
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Porcelain
Mounting Position	Vertical
Number of Flange Mounting Holes	12
Test Tap	Yes
Top Terminal Plating	Silver Plated
Top Terminal Type	Threaded
Type	Condenser Bushings

Dimensions

Above Flange Length	89.81 in
Below Flange Length	59.5 in
Diameter - Below Flange Maximum D <gt/> 1"	10.12 in
Diameter - Below Flange Maximum P	10.12 in
Diameter - Bottom Terminal Bolt Circle	3.75 in & 6.75 in
Diameter - Bottom Terminal Bolt Holes	3/8-16 & 1/2-13
Diameter - Bottom Terminal Outside	8.25 in
Diameter - Live Part Top	10.50 in
Diameter - Top Terminal Outside	2-12
Dimensions	149.31 in x 23.00 in x 149.31 in
Effective Length - Top Terminal	3.00 in
Flange Mounting Hole Bolt Circle	21 in
Flange Mounting Hole Diameter	1.25 in
Flange Outside Diameter	23 in
Height	149.31 in
Length	149.31 in
Length - Ground Shield	26.75 in
Length - Live Part Top	7.56 in
Length - Minimum Oil Immersion Level	26.75 in
Sealing Surface Outside Diameter	19.62 in
Weight	740 lb
Width	23 in

Electrical Ratings

BIL	900 kV
Current Rating	2500 A
Minimum Creepage	230 in
Minimum Strike	78 in
kV Class	230 kV

Certifications And Compliance

Industry Standard(s)

IEEE

Product Assets

[Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)

[Installation Manuals - Instruction Manual for POC® Bushings](#)

[Sales Drawings - Transformer- Breaker Interchangeable](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
PCOR-POC900G2500SX17-SPEC-EN | REV 6/2024