

# HUBBELL

## Power Systems

### PRC 89 Series Bushing - 15kV

By PCORE Electric  
 Catalog # [B-0891236570](#)

PRC® 15kV-2000A Transformer-Circuit Breaker Bushing, Paper-Resin-Capacitor Type, Rated per IEEE C57.19.01, Bottom Connected for Air-to-Oil Applications, 21.00" Min. Oil Immersion Level



#### Features

- Resin-impregnated paper wound core with external porcelain insulator
- High creep upper porcelain, High seismic

#### General

Application	Transformer-Oil Circuit Breaker
Bottom Terminal Type	Threaded
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Porcelain
Mounting Position	Vertical
Number of Flange Mounting Holes	3
Test Tap	Yes
Top Terminal Type	Threaded
Type	Condenser Bushings

#### Dimensions

Above Flange Length	15.25 in
Below Flange Length	28 in
Diameter - Below Flange Maximum D > 1"	3.12 in
Diameter - Below Flange Maximum P	3.38 in
Diameter - Bottom Terminal Outside	1 1/2-12
Diameter - Live Part Top	3.88 in
Diameter - Top Terminal Outside	1 1/2-12
Effective Length - Bottom Terminal	2.12 in
Effective Length - Top Terminal	2.12 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.5 in
Length	43.25 in
Length - Ground Shield	21.00 in
Length - Live Part Top	3.69 in
Length - Minimum Oil Immersion Level	21.00 in
Sealing Surface Outside Diameter	6.12 in
Weight	60 lb

#### Electrical Ratings

BIL	110 kV
Current Rating	2000 A
Minimum Creepage	21 in
Minimum Strike kV Class	10 in
	15 kV

## Certifications And Compliance

Industry Standard(s)

IEEE

## Product Assets

[Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)

[Installation Manuals - Instruction Manual for PRC® Bushings](#)

[Sales Drawings - 89123-65 and 70 Rev 04-08-20](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
PCOR-B0891236570-SPEC-EN | REV 6/2024