

**PRC 89 Series Bushing - 15kV**

By PCORE Electric  
Catalog # [B-89112-62-70](#)

PRC® 15kV-1200A Transformer-Circuit Breaker Bushing, Paper-Resin-Capacitor Type, Rated per IEEE C57.19.01, Horizontal mount, Bottom Connected for Air-to-Oil Applications, 16.50" Min. Oil Immersion Level



**Features**

- Resin-impregnated paper wound core with external porcelain insulator
- High creep upper porcelain, High seismic

**Application**

Transformer-Oil Circuit Breaker

**General**

Bottom Terminal Type	Threaded
Catalog Number	B-89112-62-70
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Porcelain
Mounting Position	Horizontal / Vertical
Number of Flange Mounting Holes	4
Test Tap	Yes
Top Terminal Plating	Silver Plated
Top Terminal Type	Threaded
Type	Condenser Bushings

**Dimensions**

Above Flange Length	15 in
Below Flange Length	16.5 in
Diameter - Below Flange	2.62 in
Maximum D <gt; 1"	
Diameter - Below Flange	3.38 in
Maximum P	
Diameter - Bottom Terminal Outside	1 1/8-12

Diameter - Live Part Top	3.25 in
Diameter - Top Terminal Outside	1 1/8-12
Effective Length - Bottom Terminal	2.12 in
Effective Length - Top Terminal	2.12 in
Flange Mounting Hole Bolt Circle	7.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	8.5 in
Length	31.5 in
Length - Ground Shield	10.00 in
Length - Live Part Top	3.66 in
Length - Minimum Oil	10.00 in
Immersion Level	
Sealing Surface Outside Diameter	6.25 in
Weight	30 lb

**Electrical Ratings**

BIL	110 kV
Current Rating	1200 A
Minimum Creepage	17 in
Minimum Strike	9.5 in
kV Class	15 kV

**Certifications And Compliance**

Industry Standard(s)	IEEE
----------------------	------

**Product Assets**

- [Catalogs - PCORE® Capacitance-Graded Bushings, Test Terminals and Services](#)
- [Installation Manuals - Instruction Manual for PRC® Bushings](#)
- [Sales Drawings - 89112-62/70 Rev 05-08-96](#)
- [Specifications - B891126270](#)