

Adhesive Connector, LC, Multimode, White, 6 Pack

By Hubbell Premise Wiring
Catalog # [FCLCMM](#)

Fiber Connector, OPTIchannel Connector, LC Simplex Multi Mode, White, 6 Pack.

Features

- Rugged Crimp Strain Relief
- Compatible with Heat Cure Epoxy
- 900 micron and 3.0mm Cable Applications

Application

Interconnect

Performance

- Optical - Insertion loss - 0.5dB typical, 0.75dB max
- Optical - Multimode return loss - 20dB minimum
- Optical - Singlemode return loss - 26dB minimum
- Environmental - Operating temperature - 0 °C to +75 °C
- Mechanical - Mating durability - 500 cycles, < 0.75dB

General

Adapter Type	LC
Catalog Number	FCLCMM
Color	White
Connector Type	LC
EU RoHS Indicator	Yes
Enclosure Type	Various
Environmental Conditions	Indoor
Item Type	LC
Material	Ceramic
Material - Mounting Hardware	Fiber Termination, Field Polish
OEM Brand Name	Hubbell Premise Wiring
Repeatability	0.1 dB
Service Life	500 matings
Specifications	<ul style="list-style-type: none">• Connector body - Nickel plated brass• Crimp insert - Nickel plated brass with polymer core



Style	Adhesive
Sub Brand	OptiChannel
Temperature Rating	0C to 70C
UPC	662620830759

Dimensions

Display Size	1.25 mm
--------------	---------

Electrical Ratings

Connectivity	Fiber Optic Connector
Insertion Loss	0.75 dB Max
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	Multimode

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">• Telcordia GR-326-CORE• TIA-568-C.3• TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog Page - PREM G16](#) [Catalog Page](#)
[Catalogs - Premise Wiring](#) [Catalog](#)
[Specifications - FCLCMM](#)