

HUBBELL

Power Systems

PRC type bushing - 46kV

By PCORE Electric
 Catalog # [B-89401-70](#)

PRC® 46kV- 400A Transformer-Circuit Breaker Bushing, Paper-Resin-Capacitor Type, Rated per IEEE C57.19.01, Draw lead Connected for Air-to-Oil Applications , 16.50" Min. Oil Immersion Level



Features

- Resin-impregnated paper wound core with external porcelain insulator
- High creep upper porcelain, High seismic

General

Application	Transformer
Color	Gray
Immersion Type - Above Flange	Air
Immersion Type - Below Flange	Oil
Material - Flange	Aluminum
Material - Insulation	Porcelain
Mounting Position	Vertical
Number of Flange Mounting Holes	4
Test Tap	Yes
Top Terminal Plating	Silver Plated
Top Terminal Type	Threaded
Type	Condenser Bushings

Dimensions

Above Flange Length	28.62 in
Below Flange Length	27 in
Diameter - Below Flange Maximum D <gt;/> 1"	4.00 in
Diameter - Below Flange Maximum P	4.50 in
Diameter - Live Part Top	4.50 in
Diameter - Top Terminal Outside	1 1/8-12
Dimensions	55.62 in x 10.63 in x 55.62 in
Effective Length - Top Terminal	2.50 in
Flange Mounting Hole Bolt Circle	8.25 in
Flange Mounting Hole Diameter	0.88 in
Flange Outside Diameter	10.62 in
Height	55.62 in
Length	55.62 in
Length - Drawlead Above Flange	24.75 in
Length - Ground Shield	16.50 in
Length - Live Part Top	5.81 in
Length - Minimum Oil Immersion Level	16.50 in
Sealing Surface Outside Diameter	7.25 in
Stud Inside Diameter	1 in
Weight	83 lb
Width	10.63 in

Electrical Ratings

BIL	250 kV
Current Rating	400 A
Minimum Creepage	49 in
Minimum Strike	21 in
kV Class	46 kV

Certifications And Compliance

Industry Standard(s)

IEEE

Product Assets

Catalogs - PCORE® Capacitance-Graded Bushings, Test
Terminals and Services

Sales Drawings - 89401 and 70 Rev 04-01-20

Sales Drawings - PRC Bushing



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
PCOR-B8940170-SPEC-EN | REV 6/2024