

# HUBBELL

## Power Systems

### 600 Series - 48" Presloped Drain, Sloped Channel

By Polycast  
Catalog # [DP0602](#)

The versatile design of the 600 Series allows for flow rates equal to or greater than most larger poured-in-place trench drains (470 GPM per outlet attainable with proper components). It is ideally suited for a variety of commercial and industrial applications. Optional Vinyl Ester channels are available for use in harsh chemical or high temperature applications. DIN Class A - D



\*Representative Image

#### Features

- Designed to have flow rates equal to or greater than most larger poured-in-place trench drains.
- The Precast trench sections and grates are made up of 2' and 4' lengths.
- Available in either polyester or Vinyl Ester polymer concrete.
- Frames are available for use with hard wheel traffic.

#### General

Available Options	Available in Vinyl Ester for corrosive or high temperature applications
Color	Gray
Material	Polyester Polymer Concrete
Series	600 Series
Type	Channels/600 Series
UPC	662037207960

#### Dimensions

Dimensions	48 in x 6 in x 5 in
Height	5 in
Length	48 in
Weight	45 lb
Width	6 in

#### Product Assets

- [Catalogs - Trench Drains](#)
- [Sales Drawings - DP06\\_\\_ Model](#)
- [Video - Hubbell Power Systems Getting Real About Rust](#)