

HFCD1 Series Indoor Tight Buffer
Distribution, 24 strand, Plenum,
OS2, SM, Yellow Jacket

By Hubbell Premise Wiring
Catalog # [HFCD1024PS](#)



HFCD1 Series Indoor Tight Buffer Distribution, 24 strand, Plenum,
OS2, SM , Yellow Jacket.

Application

Data Tranmission

General

Attenuation	0.5/0.4 Db per Kilometer
Cable Rating	Plenum
Catalog Number	HFCD1024PS
Color	Yellow
Material - Jacket	PVC
Specifications	• Armor - None • Cable Diameter in (mm) - 0.32 (8.1) • Cable Weight (lb/kft) - 43 • Construction - Single Unit, Aramid Strength Member • Fiber Coating - 900 Micron PVC Tight Buffer
Sub Brand	Fiber Optics
Temperature Rating	0 Degrees C to 70 Degrees C
Type	Cable
UPC	662620332048

Electrical Ratings

Wavelength1310/1550 Nanometers

Conductor Related

Fiber Size	OS2
Fiber Type	OS2, SM
Number of Fibers	24

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-6 • Telcordia GR-409 • TIA-568.3-D

Product Assets

[Catalog Page - PREM I03 Catalog Page](#)
[Catalog Page - PREM I3 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - Fiber Optic Cable Guide](#)
[Specifications - HFCD1024PS](#)