

600 Series - 48" Presloped Drain,
Sloped Channel

By Polycast
Catalog # [DP0621](#)

The versatile design of the 600 Series allows for flow rates equal to or greater than most larger poured-in-place trench drains (470 GPM per outlet attainable with proper components). It is ideally suited for a variety of commercial and industrial applications. Optional Vinyl Ester channels are available for use in harsh chemical or high temperature applications.DIN Class A - D

Features

- Designed to have flow rates equal to or greater than most larger poured-in-place trench drains.
- The Precast trench sections and grates are made up of 2' and 4' lengths.
- Available in either polyester or Vinyl Ester polymer concrete.
- Frames are available for use with hard wheel traffic.

General

| | |
|-------------------|---|
| Available Options | Available in Vinyl Ester for corrosive or high temperature applications |
| Catalog Number | DP0621 |
| Color | Gray |
| Material | Polyester Polymer Concrete |



*Representative Image

| | |
|--------|---------------------|
| Series | 600 Series |
| Type | Channels/600 Series |

Dimensions

| | |
|------------|-------------------------|
| Dimensions | 48 in x 6.25 in x 11 in |
| Height | 11 in |
| Length | 48 in |
| Weight | 68 lb |
| Width | 6.25 in |

Product Assets

- [Catalogs - Trench Drains](#)
- [Specifications - Polycast Quick Quote](#)
- [Specifications - DP0621](#)
- [Video - Hubbell Power Systems Getting Real About Rust](#)