

HFCD1 Series Indoor Tight Buffer
Distribution, 24 strand, Riser, OM1,
MM, Orange Jacket

By Hubbell Premise Wiring
Catalog # [HFCD1024R6](#)

HFCD1 Series Indoor Tight Buffer Distribution, 24 strand, Riser,
OM1, MM , Orange Jacket.



Application

Data Tranmission

General

Attenuation	3.5/1.5 Db per Kilometer
Cable Rating	Riser
Catalog Number	HFCD1024R6
Color	Orange
Material - Jacket	PVC
Specifications	• Armor - None • Cable Diameter in (mm) - 0.32 (8.1) • Cable Weight (lb/kft) - 43 • Construction - Single Unit, Aramid Strength Member • Fiber Coating - 900 Micron PVC Tight Buffer
Sub Brand	Fiber Optics
Temperature Rating	-20 Degrees C to 70 Degrees C
Type	Cable
UPC	662620246970

Electrical Ratings

Wavelength	850/1300 Nanometers
------------	---------------------

Conductor Related

Fiber Size	OM1
Fiber Type	OM1, MM
Number of Fibers	24

Certifications And Compliance

Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-4 • Telcordia GR-409 • TIA-568.3-D
----------------------	---

Product Assets

- [Catalog Page - PREM I03 Catalog Page](#)
- [Catalog Page - PREM I3 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - Fiber Optic Cable Guide](#)
- [Specifications - HFCD1024R6](#)