

HUBBELL

Premise Wiring

Fiber, Pigtail, Bundle, 250 Micron, Buffered Loose Tube, LC-Single Mode, 6-Fiber Strands, OS2 Fiber, 3 Meter



By Hubbell Premise Wiring
Catalog # [FHPBKLTR6LC6S](#)

Fiber, Pigtail, Bundle, 250 Micron, Buffered Loose Tube, LC-Single Mode, 6-Fiber Strands, OS2 Fiber, 3 Meter

Features

- Bundle
- 250 Micron
- Buffered Loose Tube
- LC-Single Mode
- 6-Fiber Strands

Application

Optical Signal

General

Attenuation	.75dB Per End
Boot Type	Standard Strain Relief Boot
Catalog Number	FHPBKLTR6LC6S
Connector Type	LC
Insulation	PVC
Item Type	LC-SM Pigtails
Material	Glass Fiber
Material - Insulation	Flame Redardant PVC
Material - Jacket	Flame Redardant PVC
Plug Type	LC-MM, 6F, 250LT, OS2
Temperature Rating	TIA 568-C.3
UPC	662620363134

Dimensions

Display Size	9 Micron
Length (Meters)	3 m
Outside Diameter	0.2
Pitch	6

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Conductor Type	Glass
Fiber Type	Riser
Mode	OS2
Number of Fibers	6
Wire Size	9 Micron
Wire Type	Multimode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

[Catalog Page - PREM H8 CatalogPage](#)
[Catalog Page - PREM H9 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Sales Drawings - FHPBKLTR6LC - PDF](#)
[Specifications - FHPBKLTR6LC6S](#)