



# Fiber Optic Panel Adapter, 12-Fiber, 6 SC Duplex, Zircon Sleeves, Black

By Hubbell Premise Wiring  
Catalog # [FSPNSCDS6BK](#)

Fiber Optic Panel Adapter, 12-Fiber, 6) SC Duplex, Zircon Sleeves, Black.



## Application

Interconnect

## General

Color	Black
Environmental Conditions	Indoor
Material	Ceramic Zirconium
Material - Mounting Hardware	Snap-In
Performance	<ul style="list-style-type: none"><li>Optical - SM/MM insertion loss - Less than 0.50dB (0.25dB typical)</li><li>Environmental - Operating temperature - 0 °C to +75 °C</li></ul>
Service Life	500 matings
Sub Brand	OptiChannel
Temperature Rating	-40C to +85C
UPC	662620340364

## Electrical Ratings

Insertion Loss	0.30 dB
----------------	---------

## Conductor Related

Fiber Size	125 Micron
Fiber Type	Singlemode or Multimode

## Certifications and Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>TIA-568-C.3</li><li>TIA-604-FOCIS</li></ul>
----------------------	---

## Logistics

Carton Quantity	4
-----------------	---

## Product Assets

[Catalog Page - PREM G8 Catalog Page](#)  
[Catalogs - HPW CATALOG\\_2023\\_FULL](#)  
[Engineering Drawing - PREMISE\\_HWS14984C\\_ACAD](#)  
[Literature - FIBERHUBB N-Series Fiber Panels](#)  
[Sales Drawings - PREMISE\\_HWS14984C\\_SALESDRAWING](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
PREM-FSPNSCDS6BK-SPEC-EN | REV 7/2023