

HFCD1 Series Indoor Tight Buffer Distribution, 2 strand, Plenum, OM3, MM, Aqua Jacket

By Hubbell Premise Wiring

Catalog # [HFCD1002P3](#)

HFCD1 Series Indoor Tight Buffer Distribution, 2 strand, Plenum, OM3, MM , Aqua Jacket.

Application

Data Tranmission

General

Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	2000 bps
Cable Rating	Plenum
Catalog Number	HFCD1002P3
Color	Aqua
Material - Jacket	PVC
Specifications	- Armor - None - Cable Diameter in (mm) - 0.17 (4.4) - Cable Weight (lb/kft) - 12 - Construction - Single Unit, Aramid Strength Member - Fiber Coating - 900 Micron PVC Tight Buffer
Sub Brand	Fiber Optics
Temperature Rating	0 Degrees C to 70 Degrees C
Type	Cable
UPC	662620555454

Electrical Ratings

Wavelength	850/1300 Nanometers
------------	---------------------

Conductor Related

Fiber Size	OM3
Fiber Type	OM3, MM
Number of Fibers	2

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	- ANSI/ICEA S-83-596 - NFPA-262/UL910/CSA FT-6 - Telcordia GR-409 - TIA-568.3-D

Product Assets

[Catalog Page - PREM I03 Catalog Page](#)

[Catalog Page - PREM I3 CatalogPage](#)

[Catalogs - Premise Wiring Catalog](#)

[Literature - Fiber Optic Cable Guide](#)

[Specifications - HFCD1002P3](#)

