

HFCD1 Series Indoor Tight Buffer
Distribution, 12 strand, Plenum,
OM3, MM, Aqua Jacket

By Hubbell Premise Wiring
Catalog # [HFCD1012P3](#)

HFCD1 Series Indoor Tight Buffer Distribution, 12 strand, Plenum,
OM3, MM , Aqua Jacket.



Application

Data Transmission

General

Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	2000 bps
Cable Rating	Plenum
Catalog Number	HFCD1012P3
Color	Aqua
Material - Jacket	PVC
Specifications	- Armor - None - Cable Diameter in (mm) - 0.25 (6.3) - Cable Weight (lb/kft) - 35 - Construction - Single Unit, Aramid Strength Member - Fiber Coating - 900 Micron PVC Tight Buffer
Sub Brand	Fiber Optics
Temperature Rating	0 Degrees C to 70 Degrees C
Type	Cable
UPC	662620330563

Electrical Ratings

Wavelength850/1300 Nanometers

Conductor Related

Fiber Size	OM3
Fiber Type	OM3, MM
Number of Fibers	12

Certifications And Compliance

Industry Standard(s)	- ANSI/ICEA S-83-596 - NFPA-262/UL910/CSA FT-6 - Telcordia GR-409 - TIA-568.3-D
----------------------	---

Logistics

Carton Quantity	1000
-----------------	------

Product Assets

- [Catalog Page - PREM I03 Catalog Page](#)
- [Catalog Page - PREM I3 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - Fiber Optic Cable Guide](#)
- [Literature - OptiChannel HFCD1 Series Indoor Distribution Fiber Cable](#)
- [Specifications - HFCD1012P3](#)