

HFCD1 Series Indoor Tight Buffer
Distribution, 24 strand, Plenum,
OM4, MM, Aqua Jacket

By Hubbell Premise Wiring
Catalog # [HFCD1024P4](#)



HFCD1 Series Indoor Tight Buffer Distribution, 24 strand, Plenum,
OM4, MM , Aqua Jacket.

Application

Data Tranmission

General

Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	4000 bps
Cable Rating	Plenum
Catalog Number	HFCD1024P4
Color	Aqua
Material - Jacket	PVC
Specifications	• Armor - None • Cable Diameter in (mm) - 0.32 (8.1) • Cable Weight (lb/kft) - 43 • Construction - Single Unit, Aramid Strength Member • Fiber Coating - 900 Micron PVC Tight Buffer
Sub Brand	Fiber Optics
Temperature Rating	0 Degrees C to 70 Degrees C
Type	Cable
UPC	662620332031

Electrical Ratings

Wavelength	850/1300 Nanometers
------------	---------------------

Conductor Related

Fiber Size	OM4
Fiber Type	OM4, MM
Number of Fibers	24

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-6 • Telcordia GR-409 • TIA-568.3-D

Product Assets

[Catalog Page - PREM I03 Catalog Page](#)
[Catalog Page - PREM I3 CatalogPage](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - Fiber Optic Cable Guide](#)
[Specifications - HFCD1024P4](#)