

HFCD1 Series Indoor Tight Buffer
Distribution, 24 strand, Riser, OS2,
SM, Yellow Jacket

By Hubbell Premise Wiring
Catalog # [HFCD1024RS](#)



HFCD1 Series Indoor Tight Buffer Distribution, 24 strand, Riser, OS2, SM , Yellow Jacket.

Application

Data Transmission

General

Attenuation	0.5/0.4 Db per Kilometer
Cable Rating	Riser
Catalog Number	HFCD1024RS
Color	Yellow
Material - Jacket Specifications	PVC • Armor - None • Cable Diameter in (mm) - 0.32 (8.1) • Cable Weight (lb/kft) - 43 • Construction - Single Unit, Aramid Strength Member • Fiber Coating - 900 Micron PVC Tight Buffer
Sub Brand	Fiber Optics
Temperature Rating	-20 Degrees C to 70 Degrees C
Type	Cable
UPC	662620333670

Electrical Ratings

Wavelength	1310/1550 Nanometers
------------	----------------------

Conductor Related

Fiber Size	OS2
Fiber Type	OS2, SM
Number of Fibers	24

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-4 • Telcordia GR-409 • TIA-568.3-D

Product Assets

- [Catalog Page - PREM I03 Catalog Page](#)
- [Catalog Page - PREM I3 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - Fiber Optic Cable Guide](#)
- [Specifications - HFCD1024RS](#)