

HFCD1M Series Indoor Tight Buffer
Distribution, 72 strand, Plenum, Multi-Unit,
OM4, MM, Yellow Jacket

By Hubbell Premise Wiring
Catalog # [HFCD1M12072P4](#)

HFCD1M Series Indoor Tight Buffer Distribution, 72 strand,
Plenum, Multi-Unit, OM4, MM , Yellow Jacket

Features

- Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission

Specifications

Industry Standard(s)	TIA
Conductor	
Fiber Size	OM4
Fiber Type	OM4, MM
Number Of Fibers	72
Current	
Wavelength	850/1300 Nanometers
General	
Sub Brand	Fiber Optics

Type	Cable
Cable Rating	Plenum, Multi-Unit
Material - Jacket	PVC
Specifications	• Armor - None • Cable Diameter in (mm) - 0.79 (20) • Cable Weight (lb/kft) - 238 • Construction - Multi-Unit, 12F/Unit, Central Strength Member • Fiber Coating - 900 Micron PVC Tight Buffer
	662620555621
	UPC
	Color
Yellow	
Operational	
Attenuation	3.5/1.5 Db per Kilometer
Temperature Rating	0 Degrees C to 70 Degrees C
Bandwidth	4000 bps
Product Assets	
Catalog [English]	
Catalog Page [English]	
Catalog Page [English]	

