

HUBBELL
Premise Wiring

HFCD14 Series Indoor/Outdoor Tight Buffer,
12 strand, I/O Tight Buffer Plenum, OS2, SM,
Black Jacket

By Hubbell Premise Wiring
Catalog # [HFCD14012PSBK](#)

HFCD14 Series Indoor/Outdoor Tight Buffer, 12 strand, I/O Tight Buffer
Plenum, OS2, SM , Black Jacket



Features

- Singlemode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission

Specifications

Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-6 • Telcordia GR-409 and GR-20 • TIA-568.3-D
----------------------	---

Conductor

Number Of Fibers	12
Fiber Size	OS2
Fiber Type	OS2, SM

Current

Wavelength	1310/1550 Nanometers
------------	----------------------

General

Color	Black
UPC	662620320335
Type	Cable
Sub Brand	Fiber Optics
Material - Jacket	PVC
Cable Rating	I/O Tight Buffer Plenum

Operational

Attenuation	0.5/0.4 Db per Kilometer
Temperature Rating	0 Degrees C to 70 Degrees C

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)