

HUBBELL  
Premise Wiring

HFCD14 Series Indoor/Outdoor Tight Buffer, 48 strand, I/O Tight Buffer Plenum, OM3, MM, Black Jacket

By Hubbell Premise Wiring  
Catalog # [HFCD14048P3BK](#)

HFCD14 Series Indoor/Outdoor Tight Buffer, 48 strand, I/O Tight Buffer Plenum, OM3, MM , Black Jacket

Features

- Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission

Specifications

|                      |                                                                                                                                                                   |
|----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Industry Standard(s) | <ul style="list-style-type: none"><li>• ANSI/ICEA S-83-596</li><li>• NFPA-262/UL910/CSA FT-6</li><li>• Telcordia GR-409 and GR-20</li><li>• TIA-568.3-D</li></ul> |
|----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Conductor

|                  |         |
|------------------|---------|
| Fiber Size       | OM3     |
| Fiber Type       | OM3, MM |
| Number Of Fibers | 48      |



Current

|            |                     |
|------------|---------------------|
| Wavelength | 850/1300 Nanometers |
|------------|---------------------|

General

|                   |                         |
|-------------------|-------------------------|
| Sub Brand         | Fiber Optics            |
| Type              | Cable                   |
| Cable Rating      | I/O Tight Buffer Plenum |
| Material - Jacket | PVC                     |
| UPC               | 662620332253            |
| Color             | Black                   |

Operational

|                    |                             |
|--------------------|-----------------------------|
| Attenuation        | 3.5/1.5 Db per Kilometer    |
| Temperature Rating | 0 Degrees C to 70 Degrees C |
| Bandwidth          | 2000 bps                    |

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)