

HFCDH Series Indoor Tight Buffer
Hybrid, 2 strand, 2 16 AWG
Conductor, Plenum, OS2, SM,
Yellow Jacket

By Hubbell Premise Wiring
Catalog # [HFCDH002PS216](#)



HFCDH Series Indoor Tight Buffer Hybrid, 2 strand,2 16 AWG
Conductor, Plenum, OS2, SM , Yellow Jacket

Features

- Corning ULTRA SMF-28® Singlemode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- 2 x 16 AWG Stranded Conductors for Distributed DC Power
- Pefect of Passive Optical Delivery

Application

Data Tranmission

General

Attenuation	0.5/0.4 Db per Kilometer
Cable Rating	Plenum
Catalog Number	HFCDH002PS216
Color	Yellow
Material - Jacket	PVC
Sub Brand	Fiber Optics
Temperature Rating	0 Degrees C to 70 Degrees C
Type	Cable

UPC662620340647

Electrical Ratings

Wavelength1310/1550 Nanometers

Conductor Related

Fiber Size	Single Mode
Fiber Type	OS2, SM
Number of Fibers	2

Certifications And Compliance

Industry Standard(s)TIA

Product Assets

[Case Studies - CASE STUDY | SHIPBOARD NETWORKS](#)
[Catalog Page - PREM G20 Catalog Page](#)
[Catalogs - Premise Wiring Catalog](#)
[Literature - FIBERHUBB™ Passive Optical LAN \(POL\) Solution](#)
[Specifications - HFCDH002PS216](#)