

HUBBELL
Premise Wiring

HFCD15 Series Indoor Tight Buffer
Distribution, 24 strand, OM3, MM, Plenum,
Armored, Indoor Tight Buffer Distribution,
Aqua

By Hubbell Premise Wiring
Catalog # [HFCD15024P3](#)

HFCD15 Series - Indoor Tight Buffer Distribution, 24 strand, OM3,
MM, Plenum, Armored, Indoor Tight Buffer Distribution, Aqua

Features

- Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Durable Aluminum Interlock Armor
- Premium Fiber For Enhanced Optical Performance

Application

Data Tranmission

Specifications

Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-6 • Telcordia GR-409 • TIA-568.3-D
----------------------	---

Conductor

Fiber Size	OM3
Fiber Type	OM3, MM
Number Of Fibers	24

Current

Wavelength	850/1300 Nanometers
------------	---------------------

General

Sub Brand
Type
Cable Rating
Material - Jacket
Specifications

Fiber Optics
Cable
Plenum, Armored
PVC

- Armor - Aluminum Interlock
- Cable Diameter in (mm) - 0.69 (17.4)
- Cable Weight (lb/kft) - 188
- Construction - Single Unit, Aramid Strength Member
- Fiber Coating - 900 Micron

PVC Tight Buffer
662620332130
Aqua

Operational

Attenuation	3.5/1.5 Db per Kilometer
Temperature Rating	0 Degrees C to 70 Degrees C
Bandwidth	2000 bps

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)

