

HUBBELL
Premise Wiring

HFCH5 Series - Outdoor Loose Tube, 12 strand, OS2, SM, OSP, Armored Double Jacket, Outdoor Loose Tube, Black Jacket

By Hubbell Premise Wiring
Catalog # [HFCH5012BK5](#)

HFCH5 Series - Outdoor Loose Tube, 12 strand, OS2, SM, OSP, Armored Double Jacket, Outdoor Loose Tube, Black

Features

- G.652.D Singlemode Bend-Insensitive Optical Fiber
- TIA-598-C Colored Buffer Tubes
- Gel-Free Water Blocking Construction
- Robust Design For Enhanced Optical Performance

Application

Data Transmission


Specifications

- | | |
|----------------------|---|
| Industry Standard(s) | <ul style="list-style-type: none">• ANSI/ICEA S-87-640• ANSI/TIA-758-A• Telcordia GR-20• TIA-568.3-D |
|----------------------|---|

Conductor

- | | |
|------------------|---------|
| Fiber Size | OS2 |
| Fiber Type | OS2, SM |
| Number Of Fibers | 12 |

Current



Wavelength	1310/1550 Nanometers
General	
Sub Brand	Fiber Optics
Type	Cable
Cable Rating	OSP, Armored Double Jacket
Material - Jacket	MDPE
Specifications	• Armor - Corrugated Steel • Cable Diameter in (mm) - 0.54 (13.8) • Cable Weight (lb/kft) - 112 • Construction - Armored Double Jacket Loose Tube, 6F/Tube, Central Strength Member • Fiber Coating - 250 Micron Acrylate Buffer
UPC	662620606019
Color	Black
Operational	
Temperature Rating	-40 Degrees C to 75 Degrees C