

NEXTSPEED

Cable
Indoor/Outdoor CMP Cable


HUBBELL

Features

- Designed for wet environments
- Plenum rated to eliminate transition points
- UV and chemically resistant jacket
- Water blocking barrier protects cable w/o gel

Ordering Information

Description	Color	Catalog Number	UPC
NEXTSPEED® Category 6A Indoor/Outdoor CMP Rated Cable, 1,000 ft Spool	Black	C6A10SPBK	662620349268



Listings

c(UL)us Listed Type CMP (NFPA 262),
CSA Type FT6
UL Verified TIA-568-D.2 CAT 6A

Specifications

Performance	Tested from 1 to 660 MHz
ANSI/TIA 568.2-D Category 6A Compliant; ISO/IEC 11801, 2nd ed. Class EA Compliant	Tested from 1 to 660 MHz
Conductor	23 AWG Bare Copper
Construction	0.31" O.D. Dual Layer Overall Jacket
Construction	Water Blocking Barrier
Operating Temperature Range	-40°C to +90°C (-40°F to +194°F)

Accessories

Category 6A UTP CobraLock Jack	HJU6AB
Category 6A Field Termination Plug	SP6A

Online Resources

eCatalog