

Cable
UTP Cables
NEXTSPEED®Ascent Category 10GbE Cable

HUBBELL

Features

- 10GbE Application Assurance
- Maximum Bandwidth Beyond 750MHz
- Component Compliant ANEXT Performance
- PoE and PoE+ Ready

Ordering Information

Description	Color	Catalog Number	UPC Number
NEXTSPEED®Ascent 10GbE, 4-Pair, UTP Cable, Plenum Spool	White	C6ASPW	662620201931

Listings

TIA-568-C.2 (Category 6A Component)
NEC Article 800 Compliant
UL Listed and Tested

Specifications

Wire	23 AWG Bare Solid Copper
Primary Insulation	CMP: FEP
Primary Insulation	CMR: Polyolefin
Cabling	4 Unshielded Twisted Pairs
Outer Jacket	Low Smoke PVC
Inner Jacket	PVC

Performance

Verifications	IEEE 802.3af (PoE), IEEE 802.3at (PoE+), and IEEE 802.3bt (4PPPoE) Exceeds IEEE 802.3an 10GBASE-T Link Segment Requirements
---------------	--

Applications

Data Centers 10GbE Between Devices
High-Performance Cable Applications
PoE Applications

Accessories

NEXTSPEED Ascent 10GbE Jacks **HJ6AW**
NEXTSPEED Ascent 10GbE Patch Panels **HP6App (pp=Ports)**

NEXTSPEED Ascent 10GbE Patch Cords **HC6AWyy (yy=Standard Length)**

TRANSMISSION SPECIFICATIONS, Worst Case 100 meter Channel Configuration							
TIA-568-B.2-10 Category 6A Compliant							
ISO/IEC 11801, 2nd Ed. Category 6A Compliant							
Freq. (MHz)	Insertion Loss (dB/100m)	NEXT Loss Min. (dB/100m)	PSNEXT Loss Min. (dB/100m)	ELFEXT Min. (dB/100m)	PSELFEXT Min. (dB/100m)	Return Loss Min. (dB/100m)	Delay Max. (ns/100m)
0.772	-	84.0	82.0	78.0	75.0	-	-
1.0	2.0	82.3	80.3	75.8	72.8	20.0	570
4.0	3.7	73.3	71.3	63.8	60.8	23.0	552
8.0	5.2	68.8	66.8	57.7	54.7	24.5	547
10.0	5.8	67.3	65.3	55.8	52.8	25.0	545
16.0	7.3	64.2	62.2	51.7	48.7	25.0	543
20.0	8.2	62.8	60.8	49.8	46.8	25.0	542
25.0	9.2	61.3	59.3	47.8	44.8	24.3	541
31.25	10.4	59.9	57.9	45.9	42.9	23.6	540
62.5	14.9	55.4	53.4	39.9	36.9	21.5	539
100.0	19.2	52.3	50.3	35.8	32.8	20.1	538
200.0	28.1	47.8	45.8	29.8	26.8	18.0	537
300.0	35.3	45.1	43.1	26.3	23.3	16.8	536
400.0	41.7	43.3	41.3	23.8	20.8	15.9	536
500.0	47.5	41.8	39.8	21.8	18.8	15.2	536

