

# OptiChannel Indoor/Outdoor Tight Buffer Cable Plenum

# HUBBELL

## Features

- E-Z Strip Buffer For Contractor-Friendly Termination
- Multi-Purpose Outdoor Duct To Building Riser Application
- Premium OM1 Fiber for Legacy Applications

## Ordering Information

Description	Fiber Type	Catalog Number	UPC Number
Indoor/Outdoor Armored Tight Buffer, 6 Fiber, Plenum, Black	OM1 Multimode	<b>HFCD19006P6BK</b>	662620658926



## Listings

ANSI/CEA S-83-596  
TIA-568.3  
NFPA-262/UL910/CSA FT-6  
Telcordia GR-409 and GR-20

## Specifications

Fiber Coating	900 Micron PVC Tight Buffer
Cable Diameter in (mm)	0.63 (16)
Cable Weight (lb/kft)	165
Construction	Single Unit, Aramid Strength Member
Aarmor	Aluminum Interlock

## Performance

### Cable Attenuation (dB/km at 850/1300 nm)

3.5/1.5

### Maximum Installation Pulling Load (lb)

150

### Maximum Operating Temperature

-4°F to +185°F (-20°C to +85°C)

### Minimum Bend Radius, In-Service in (cm)

9.5 (24)

## Accessories

Fiber Strip Tool	<b>OFSTRIP2</b>
Splice Tray, 12 Fusion	<b>STRAY12F</b>
Splice Tray, 24 Fusion	<b>STRAY24F</b>
Splice Protection Sleeves	<b>FSHST401025</b>

## Online Resources

eCatalog

