

# Grounding & Bonding Compression Lugs Single Pack

# HUBBELL

## Features

- Long barrel compression lugs are the best solution for building a low-resistant bond
- HPW lugs are die index traceable when using a properly sized die for compression
- Lugs are tin plated and have an inspection window to ensure that the conductor is fully listed



## Ordering Information

Description	Mounting Hole Size	UPC Number	Catalog Number
Compression Lugs, 4/0 AW Double Hole, 1 Pack	ID: 0.375", Spaced: 1 in	662620619361	HGBL40DB1

## Listings

c-UL-us Listed  
TIA-607 Compliant

## Specifications


Material	Tin-Plated Copper
Barrel Color	Purple
Die Index #	15
Bend Angle	Straight
Lug Mount Style	DB

## Accessories

Manual Crimp Tool	HMD7
X-Die for Manual Tool	HX25RT
12 Ton Power Crimp Tool	HPAT750LI
U-Die for Power Tool	HU25RT

## Resources

Customer Use Drawing  
Grounding & Bonding Brochure



### Dimensions in. (mm)

A	4" (101)
B	1" (26)
C	0.4" (10)
D	1" (25)

