

Wall Mount Cabinets

HLQ Series, General Use Center Swing Wall Mount Cabinet

HUBBELL

Features

- Locking Front Door and Center Section
- Two pairs of adjustable threaded rails
- U-Knockouts for installing punched down patch panels without disconnecting
- All sections bonded together

Ordering Information

Description	Depth	UPC Number	Catalog Number
Rack 25 Units	24"	662620617763	HLQ48M



Listings

EIA/ECA-310-E Universal Mounting Pattern

Specifications

Enclosure Shell Material	16 gauge C.R. Steel
Mounting Rails	12 gauge C.R. Steel
Material Finish	Black Powder Coat
Rail Type	#12-24 Threaded

Performance

Load Capacity	350 lb
Rack Units	25
Front Door	Reversible, Mesh
Mounting	Slotted holes to align with 16" spaced studs

Accessories

Horizontal rack bonding bus bar	HBBBHR19KT
Fan Kit	HLQFK
1U Horizontal cable manager	HS13C
8" Velcro Straps	HPWCVFBK8

Resources

Customer Drawing	
Brochure	
HEQ Sheet	

