

## NEXTSPEED

### Category 6 Component

### Surface Mount Panel

#### Features

- 4 dB min NEXT Margin 1 -250 MHz over TIA and ISO Channel Specifications
- Qualified to 150% of 802.3bt PoE Current Level
- Continuous Third Party Verification Program

#### Ordering Information

Description	Color	Catalog Number	UPC
NEXTSPEED Category 6 Component Surface Mount Panel, 12-Port, Category 6,	Black	HP612	662620247144

#### Listings

TIA-568-C.2 Category 6 component  
ISO/IEC 11801/60603-7-41 6 component  
Third Party tested for TIA 568-C.2 requirements. Component/link/channel Category 6 and ISO/IEC 11801 Class E  
Mechanical: Verified to TIA-568-C.2  
UL Listed 1863, UL 94 V-0 Flammability Rating ISO9001-2008 manufacturing process

#### Specifications

Nose Contact	Beryllium copper with precious metal plating with nickel under-plating
Rear IDC Contact	Phosphor bronze with 100 micro-inch lead free tin plating over nickel under plating
Panel Material	14 ga. Steel rolled-edge construction
Mounting	Dimensions and mounting holes per CEA-310-E

#### Performance

##### Electrical

NEXT margin over TIA 568 -C.2 and ISO 11801 Class E channel specifications 1-250MHz  
Exceeds component requirements of TIA-568-C.2 Category 6 and IEC Category 6 components  
Designed and tested for 1.5A of continuous current per pair

##### General Information

Manufacturing: 100% factory tested  
Universal wiring (T568A or T568B)  
Integrated labeling and icon slots for 606-B compliance


##### Mechanical

Mating Cycle: 2000+ with FCC 8-position plug

#### Applications

IEEE 802.3b 1000GBASE-T  
IEEE 802.3bt PoE+  
IEEE 802.3bt 4PPoE Power over Ethernet  
TIA TSB-155 10GbE Over 55 Meters  
Backwards compatible with Category 5E hardware and applications

# HUBBELL



#### Accessories

Category 6 Component Jack	HXJ6B
Category 6 Patch Cord	HC6B03
Category 6 Panel Replacement Adaptor	HP6M6
Category 6 UTP Cable	C6SRB

#### Online Resources

Customer Use Drawing  
eCatalog

