



HFCD1 Series Indoor Tight Buffer Distribution, 12 strand, Riser, OM1, MM , Orange Jacket

By Hubbell Premise Wiring
Catalog Number [HFCD1012R6](#)

HFCD1 Series Indoor Tight Buffer Distribution, 12 strand, Riser, OM1, MM , Orange Jacket.



Features

- Corning ClearCurve® Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission

General

Attenuation	3.5/1.5 Db per Kilometer
Cable Rating	Riser
Color	Orange
Material - Jacket	PVC
Sub Brand	Fiber Optics
Temperature Rating	-20 Degrees C to 70 Degrees C
Type	Cable
UPC	662620246963

Electrical Ratings

Wavelength 850/1300 Nanometers

Conductor Related

Fiber Size OM1
Fiber Type OM1, MM
Number Of Fibers 12

Certifications and Compliance

Industry Standard(s)

- ANSI/ICEA S-83-596
- NFPA-262/UL910/CSA FT-4
- Telcordia GR-409
- TIA-568.3-D

Product Assets

[Catalog Page - Premise Catalog Page I-3](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-HFCD1012R6-SPEC-EN | REV 5/2023