

PROClick Connector, LC, OM1,
Beige, 12 Pack

By Hubbell Premise Wiring
Catalog # [FCLC900K62M12](#)



Features

-
-

Performance

- Optical - Insertion loss - 0.5dB (0.35dB typical), 0.75dB max
- Optical - Mating durability - 500 cycles <
- 0.1dB change
- Optical - Multimode return loss - 35dB Typ, 22dB minimum
- Optical - Singlemode return loss - 55dB Typ, 40dB minimum
- Environmental - Operating temperature - 0 °C to +70 °C

General

Adapter Type	LC
Catalog Number	FCLC900K62M12
Color	Beige
Connector Type	LC
EU RoHS Indicator	Yes
Enclosure Type	Various
Item Type	LC
Material	Ceramic
Material - Mounting Hardware	Fiber Termination, No Polish
Repeatability	0.1 dB
Service Life	500 matings
Specifications	• Cable Type - 900/250 QM • Ferrule Material - Zirconia ceramic, UPC polish • Fiber Type - 62.5QM, OM1
Style	PROclick
Sub Brand	OptiChannel
Temperature Rating	0C to 70C
UPC	662620224145

Dimensions

Display Size	1.25 mm
--------------	---------

Electrical Ratings

Connectivity	Fiber Optic Connector
Insertion Loss	0.75 dB Max
Return Loss	26

Conductor Related

Fiber Size	125 Micron
Fiber Type	OM1, MM

Certifications And Compliance

Industry Standard(s)	• Telcordia GR-326-CORE • TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Logistics

Carton Quantity	10
Pallet Quantity	1680

Product Assets

- [Brochures - Fiber Connectivity Product Guide](#)
- [Catalog Page - PREM G3 CatalogPage](#)
- [Catalog Page - PREM G03 Catalog Page](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - PROclick® Fiber Connectors](#)
- [Specifications - FCLC900K62M12 Specification Sheet English](#)
- [Specifications - FCLC900K62M12 Specification Sheet French](#)
- [Video - ProClick Fiber Optic Connector Installation](#)